



Optique Peter

OPTICAL & MECHANICAL ENGINEERING

PRISM GLASSES



Prism Glasses and stand



Prismatic Stand

- ◆ 500 x 600 mm stand
- ◆ Telescopic column

Prismatic glasses right or left shift

- ◆ Standard deviations: 4° - 5° - 6° - 8° - 10° - 12° - 15°
- ◆ Deviation upon request, from 1° to 15°, right or left shift
- ◆ No deviation "placebo" glasses:
 - "Light" glasses with 4 mm thick glass
 - "Heavy" glasses, same weight and glass thickness than 10° prismatic

Prism Glasses for MRI scanner applications

- ◆ Adjustable headband to ensure a perfect fit for all head sizes
- ◆ Shutter for single eye use
- ◆ No metal part for MRI scanner application
- ◆ Standard deviations: 10°
- ◆ Deviation upon request, from 1° to 15°, right or left shift
- ◆ No deviation "placebo" glasses

